

NOTE: Tee fittings are standard with Viton seals. Saddles are standard with Buna seals. The 8225 and 8226 Compact Conductivity meters will only work in 1 1/4" thru 4" and the 8205 Compact PH systems will only work 1/2" thru 4" (8205 Compact system for 4" – 6" pipe available per special request).

Size	Sensor length	Item no.
PVC True Union Tee's (ASTM)		
1/2"	Short	428682T
3/4"	Short	428683U
1"	Short	428684V
1 1/4"	Short	428685W
1 1/2"	Short	428686X
2"	Short	428687Y
PVC Saddles (ASTM pipe)		
2 1/2"	Short	413469W
3"	Short	413470T
4"	Short	US50B20
6"	Long	US50B17
8"	Long	US50B42
Stainless Steel Tee's (NPT female)		
1/2"	Short	428742E
3/4"	Short	428743F
1"	Short	428744G
1 1/4"	Short	428745H
1 1/2"	Short	428746A
2"	Short	428747B
Stainless Steel Weld-o-lets		
1 1/2"	Short	418110X
2"	Short	418111L
2 1/2"	Short	418112M
3"	Short	418113N
4"	Short	418114P
5"	Short	418115Q
6"	Short	418116R
8"	Short	418117J
10"	Long	418756A
12"	Long	420070G
14"	Long	416637R
16"	Long	416637R

Size	Sensor length	Item no.
Stainless Steel Tee's w/ ANSI B 16.5 Flanges		
1/2"	Short	428778J
3/4"	Short	428779K
1"	Short	428780H
1 1/4"	Short	428781W
1 1/2"	Short	428782X
2"	Short	428783Y
Brass Tee's (NPT female)		
1/2"	Short	428718E
3/4"	Short	428719F
1"	Short	428720C
1 1/4"	Short	428721Z
1 1/2"	Short	428722S
2"	Short	428723T
Carbon Steel Saddles		
2"	Long	US50B49
3"	Long	US50B32
4"	Long	US50B33
5"	Long	US50B34
6"	Long	US50B35
8"	Long	US50B36
10"	Long	US50B37
12"	Long	US50B38
Carbon Steel Weld-o-lets		
2"	Long	US50B61
2 1/2"	Long	US50C34
3"	Long	US50C35
4"	Long	US50B27
5"	Long	US50B28
6"	Long	US50B29
8"	Long	US50B30
10"	Long	US50B31
12"	Long	US50C55

Size	Sensor length	Item no.
PVC Solvent Spigot (metric pipe only)		
15mm	Short	428676C
20mm	Short	428677D
25mm	Short	428678N
32mm	Short	428679P
40mm	Short	428680D
50mm	Short	428681S
PE Weld-O-Lets (metric pipe only)		
65mm	Short	418642G
80mm	Short	418643H
100mm	Short	418644A
150mm	Long	418645B
200mm	Long	418646C
250mm	Long	418647D
300mm	Long	418648N
350mm	Long	418649P
400mm	Long	418598V
Polypropylene True Union Tee's (metric pipe only)		
15mm	Short	428688H
20mm	Short	428689A
25mm	Short	428690F
32mm	Short	428691U
40mm	Short	428692V
50mm	Short	428693W
Polypropylene Weld Ends (metric pipe only)		
15mm	Short	428694X
20mm	Short	428695Y
25mm	Short	428696Z
32mm	Short	428697S
40mm	Short	428698B
50mm	Short	428699C
Polypropylene Weld-o-lets (metric pipe only)		
65mm	Short	418650L
80mm	Short	418651H
100mm	Short	418652A
150mm	Long	418653B
200mm	Long	418654C
250mm	Long	418655D
300mm	Long	418656E
350mm	Long	418657F

Size	Sensor length	Item no.
Polypropylene Saddles (metric pipe only)		
50mm	Long	425138N
65mm	Long	425139P
80mm	Long	425140U
100mm	Long	425141R
125mm	Long	425143K
150mm	Long	425144L
200mm	Long	425416D
PVDF True Union Tee's (metric pipe only)		
15mm	Short	418534L
20mm	Short	418535M
25mm	Short	418536N
32mm	Short	418537P
40mm	Short	418538Y
50mm	Short	418539Z
PVDF Weld Ends (metric pipe only)		
15mm	Short	428706B
20mm	Short	428707C
25mm	Short	428708M
32mm	Short	428709N
40mm	Short	428710A
50mm	Short	428711X